



HOW TO MEASURE YOUR VEHICLE FOR THE VARIOCAGE

Check to see if your vehicle has a raised sill at the rear cargo entrance. If the sill is raised, you should put something flat under the cage so its doors can open correctly. We recommend rigid foam board insulation to minimize interference with your car's crumple zone. The floor of the cargo area should be flat.



The Variocage is adjustable in length. The slope of the front, back, and sides are angled so it can easily fit in a typical cargo area. If you have a door with a steep angle, it may not close properly with the crate fully extended. Consider the final adjusted length of the cage to be sure it will offer enough space for your dog.

1. Measure the narrowest usable area across the floor of the cargo area where you would position the crate (A)

(Note: The narrowest usable area is often between the rear wheel wells or at the bottom of the cargo door entrance.)

2. Measure the top of the cargo area which is typically narrower than the usable floor space (B)

(Note: The left and right side of the cage are angled. Total cage width is approximately 4" narrower at the top.)

3. Measure the usable length of the cargo floor from the back seat to the door sill (C)

(Note: The front and back of the cage are angled. Total cage length is approximately 12" narrower at the top.)

4. Measure the height from the cargo floor to the lowest point at the top of the cargo door entrance (D)

(Note: Be sure to measure the shortest point which is often at the sides of the cargo entrance not in the middle.)

	Telescoping Length (min-max)	Width	Height
Variocage MiniMax			
390 - MiniMax (L)	570-770mm	440mm	455mm
366 - MiniMax (XL)	570-770mm	555mm	455mm
Variocage Compact*			
367 - Compact (L)	600-820mm	555mm	650mm
368 - Compact (XL)	600-820mm	700mm	650mm
Variocage Single			
363 - Single (L)	760-1030mm	555mm	650mm
376 - Single (XS)	730-990mm	555mm	590mm
380 - Single (XL)	810-1030mm	700mm	715mm
381 - Single (MAX)	920-1160mm	700mm	845mm
Variocage Double			
377 - Double (S)	730-990mm	930mm	590mm
383 - Double (M)	760-1030mm	930mm	650mm
361 - Double (L)	760-1030mm	990mm	650mm
364 - Double (XL)	810-1030mm	990mm	715mm
365 - Double (XXL)	810-1030mm	1060mm	715mm
369 - Double (MAX)	920-1160mm	1060mm	845mm

*The Variocage Compact is designed to work with a raised sill